

石綿(アスベスト)含有部品使用の冷凍冷蔵庫 型式一覧表(1)

型式					
CHRA-41	R-12A2	R-25VC	R-37V3	R-212D	R-C12MA
CHRB-35KL	R-12A3	R-25VCL	R-37V3L	R-213DM	R-C37MVP
CHRB-35KR	R-12A3-1	R-25VJ	R-37V7	R-214M	R-C37V4
R-2MS	R-12A6	R-25VS	R-37V7-1	R-220KT	R-C372V
R-2MSL	R-12A6-1	R-25VSL	R-37V7L	R-250VR	R-C372V-1
R-4MS	R-12BWS	R-25VT	R-37V7L-1	R-250VS	R-C372V-2
R-4MSL	R-12BWT	R-25VTL	R-38MVP2	R-252V2	R-C372VL
R-5G1	R-12NA	R-26TLV	R-38MVP2L	R-253KR	R-C372VL-1
R-5G6	R-12RA	R-26TLVL	R-38PAM	R-253KS	R-C372VL-2
R-5GR	R-12TA	R-26V3	R-38PAML	R-253VR	R-CD40NPAM
R-5GS	R-12X2	R-26V6	R-40CXT	R-254M	R-CD40NPAML
R-5MP	R-14T1	R-26V6-1	R-41EPAM	R-255M	R-CD46NPAM
R-5MP-1	R-14T2	R-26V6-2	R-41EPAML	R-258VR	R-CD46NPAML
R-5P1	R-15MWT	R-26V6L	R-42MVK	R-307DR	R-CF42TPAM
R-5TP	R-15NWT	R-26V6L-1	R-42MVP1	R-307KR	R-CF44RPAM
R-8C	R-15RMWT	R-26V6L-2	R-42MVP1L	R-307VS	R-CK40EPAM
R-8C1	R-15RNWT	R-26VLV	R-42TST	R-310DS	R-CK40EPAML
R-8G4	R-15RWTL	R-26VLVL	R-43DVS	R-310VE	R-CK40MPAM
R-8GS	R-15RWTR	R-31BVR	R-43MVP	R-319VS	R-CK40MPAML
R-8JT2	R-15SWT	R-31DJ	R-43MVP-1	R-330KS	R-CK40RPAM
R-8JT3	R-15SWTL	R-31JS	R-43MVPL	R-330VR	R-CK40RPAML
R-8K1	R-15TWT	R-31VJ	R-43MVPL-1	R-330VS	R-CK46EPAM
R-8KS	R-15WT	R-32MVP1	R-43TS	R-359XES	R-CK46EPAML
R-8KT	R-16A2	R-32MVP1L	R-44G3	R-360DR	R-CK46MPAM
R-8MP	R-16A6	R-32MVP1M	R-44MVP2	R-360M	R-CK46MPAML
R-8MP-1	R-16WS	R-32MVP2	R-44MVP2L	R-370FDS	R-CK46RPAM
R-8MT	R-17A1	R-32MVP2L	R-44PAM	R-370K	R-CK46RPAML
R-8MWR	R-17AS	R-32MVP3	R-44PAML	R-370K-1	R-CS34MPAM
R-8NT	R-17AT1	R-32MVP3L	R-45SXR	R-370SDS	R-CS34SPAM
R-8P1	R-17H1	R-33BS	R-45SXS	R-372D	R-CS34SPAML
R-8RT	R-17HT	R-33V1	R-45XR	R-372SD	R-CS36MVP1
R-8S	R-22A1	R-33V1K	R-45XS	R-374M	R-CS36MVP1L
R-8ST	R-22A2	R-33V1L	R-45XSKE	R-375M	R-CS38MVP2
R-8T	R-22A5	R-33VAR	R-45XSKT	R-375M1	R-CS38MVP2L
R-8T2	R-22A6	R-35VB	R-45XT	R-382SP	R-CS41EPAM
R-8T3	R-22AS	R-35VBL	R-48TA	R-382SPL	R-CS41EPAML
R-8T3D	R-22AT	R-35VC	R-51ST	R-413DM	R-CS41X
R-8T4	R-22MAR	R-35VCL	R-57	R-424M	R-CS41XT
R-8T6	R-22MYK	R-36DER	R-81	R-426	R-CS42MVP1
R-8T6-1	R-22NYK	R-36MVP1	R-82F	R-437	R-CS42MVP1L
R-8W1	R-22NYK-1	R-36MVP1L	R-82FN	R-447	R-CS43MD6
R-8W2	R-22RYK	R-37D1	R-84F	R-448	R-CS43MVP
R-8W3	R-22RYK-1	R-37D1L	R-84FK	R-1205M	R-CS43MVP1
R-8W3-1	R-22YK	R-37DDR	R-84FNB	R-1205M-1	R-CS43MVPL
R-8WS	R-23RA	R-37KA	R-84NP	R-3035M	R-CS44MVP2
R-8WT	R-23TA	R-37MVP	R-84NRS	R-3535M	R-CS44MVP2L
R-8YT	R-25AC	R-37MVPL	R-85F	R-4035M	R-CS44PAM
R-9G6	R-25V1	R-37SJS	R-85FNB	R-8080MH	R-CS44PAML
R-10FW1	R-25V1L	R-37V1	R-85NP	R-A44Y	R-CS46D4
R-10FWT	R-25V2	R-37V1L	R-102D	R-B12S1	R-CS47EPAM
R-10W1	R-25V2L	R-37V2	R-103DM	R-B26TLV	R-CS47EPAML
R-10WS	R-25V5	R-37V2-1	R-122KA	R-B37DT	R-CU425D
R-10WT	R-25V5L	R-37V2L	R-123KA	R-B41D1	R-D37MVP
R-11AT	R-25VAR	R-37V2L-1	R-123KA-1	R-B42D2	R-D37NPAM

石綿(アスベスト)含有部品使用の冷凍冷蔵庫 型式一覧表(2)

型式					
R-D37NPAML	RF-U12RF	R-KF40RPAM	R-S36SKT	R-S44MVP2L	R-V40EPAM
R-D40CX1	RF-U12RFK	R-KF40SHN	R-S36SV	R-S44MVPD	R-V44MVP2
R-D40NPAM	RF-U61	R-KF50SPAM	R-S36SVL	R-S44MVPDL	R-V44PAM
R-D40NPAML	RF-U8TF	R-KX46MPAM	R-S37MVP	R-S44PAM	R-V46EPAM
R-D40X1	R-G12N	R-L36X1	R-S37MVPL	R-S44PAMD	RX-17
R-D40X1K	R-G12R	R-L36X6	R-S37SPAM	R-S44PAMD	RX-172
R-D41D1B	R-G12S	R-L37D	R-S37SPAML	R-S44PAML	R-X35VB
R-D41D1K	R-GT4500	R-LB7000	R-S37TV	R-S45MVP1	R-X37V
R-D41D1L	R-H32MV	R-LD10	R-S37TVL	R-S45MVSK1	R-X37V-1
R-D41X4	RH-82T	R-M12S2	R-S37VPAM	R-S46PAM	R-X42D4
R-D42D3	RH-83T	R-MVP37R	R-S37VPAML	R-S46PAML	R-Y372
R-D42D3L	RH-87T	R-MVP37RL	R-S38MPAM	R-S47EPAM	R-Y37V
R-D42D4	RH-87T-1	R-MVP40N	R-S38MPAML	R-S47EPAMD	R-Y37V-1
R-D42D4L	RH-127A	R-MVP40NL	R-S38MVP2	R-S47EPAMD	R-Y380MV
R-D42MVP1	RH-127A-1	R-MVP40R	R-S38MVP2L	R-S47EPAML	R-YS45RPAM
R-D42MVP2	RH-162A	R-MVP40RL	R-S38MVPD	R-S50PAM	R-Z37V
R-D437M	RHD-10	R-MVP46N	R-S38MVPDL	R-S421T	R-Z37V1
R-D43MVP	RHD-20	R-MVP46NL	R-S38NPAM	R-S421TL	R-Z37V3
R-D43MVP-1	R-J44MV	R-MVP46R	R-S38NPAML	R-S361MV	R-Z42MVP1
R-D44MVP2	R-J44MVL	R-MVP46RL	R-S38PAM	R-S361MVL	
R-D44PAM	R-J426	R-MVP200	R-S38PAMD	R-S380MPAM	
R-D46NPAM	R-K37MPAM	R-MVP220	R-S38PAMD	R-S380MPAML	
R-D46NPAML	R-K37MPAML	R-P40RV5	R-S38PAML	R-S381PAM	
R-D55X1	R-K37RPAM	R-P40RV5L	R-S38RPAM	R-S381PAML	
R-D55X6	R-K37RPAML	R-P46RV5	R-S38RPAML	R-SB38RPAM	
R-D215	R-K40EPAM	R-P46RV5L	R-S39MV6	R-SF40TPAM	
R-D256	R-K40EPAML	R-R12Y	R-S39MV6L	R-SF42SPAM	
R-D257	R-K40MPAM	R-S31HRV	R-S40RPAM	R-SF42SPAM1	
R-D377	R-K40MPAML	R-S31NSM	R-S40RPAML	R-SF42SV6	
R-D377-1	R-K40NPAM	R-S31NSML	R-S40TPAM	R-SF42SV6-1	
R-D378	R-K40NPAML	R-S31NSV	R-S40TPAML	R-SF42TPAM	
R-D379	R-K40RMA1	R-S31NSVL	R-S41EPAM	R-SF42TPAM1	
R-D1208	R-K40RMA1L	R-S31SSV	R-S41EPAMD	R-SF44RPAM	
R-D3536	R-K40RPAM	R-S31SSVL	R-S41EPAMD	R-SF44SK	
R-D4036	R-K40RPAML	R-S31TSV	R-S41EPAML	R-SF44SKT	
R-D4037	R-K46EPAM	R-S31TSVL	R-S41KPAM	R-SF44SPAM	
RF-12F1	R-K46EPAML	R-S31VSV	R-S41KPAML	R-SF44TPAM	
RF-12F2	R-K46MPAM	R-S31VSVL	R-S41NPAM	R-SF44VSK	
RF-12F4	R-K46MPAML	R-S34MPAM	R-S41NPAML	R-SF47SPAM	
RF-12F6	R-K46RMA1	R-S34MPAM-1	R-S42DSKE	R-SF47SV6	
RF-15F1	R-K46RMA1L	R-S34MPAML	R-S42DSKEL	R-SF47TPAM	
RF-15F2	R-K46RPAM	R-S34NPAM	R-S42MVP1	R-SF50TAPAM	
RF-15F4	R-K46RPAML	R-S34NPAM-1	R-S42MVP1L	R-SF50TPAM	
RF-15F6	R-K50EPAM	R-S34NPAML	R-S42SPAM	R-T31TSV	
RF-23F1	R-K50MPAM	RS34NPAML-1	R-S42SPAML	R-TW8	
RF-23F2	R-K50NPAM	R-S36MVP1	R-S42TPAM	R-TW8-1	
RF-51	R-K50NPAM	R-S36MVP1L	R-S42TPAML	R-U35V5	
RF-52	R-K303V	R-S36NV	R-S43MD6	R-U35V5L	
RF-5T	R-K305V	R-S36NVL	R-S43MD6L	R-U35VSKF	
RF-67	R-K357V	R-S36RV	R-S43MVP	R-U35VSKFL	
RF-C107	R-K401R	R-S36RVL	R-S43MVP-1	R-U39MV6	
RF-U12F	R-K401RL	R-S36SK	R-S43MVPL	R-U39MV6L	
RF-U12F3	R-K460R	R-S36SKL	R-S43MVPL1	R-V38MVP2	
RF-U12FK1	R-K460RL	R-S36SKLT	R-S44MVP2	R-V38PAM	