

石綿（アスベスト）含有部品使用の除湿機 型式一覧表

発売年	型式	部品の使用部分	石綿含有質量（％）
1952	HD-100	圧縮機内部の パッキンに使用	44%
1953	FD-125		
1954	GD-125		
1955	HD-125		
1962	RD-1252		
1963	RD-2003		
1965	RD-2005		
1968	RD-758		
1970	RD-1000		
1970	RD-2003F		
1972	RD-1000L		
1973	RD-1003H		
1973	RD-1000N		
1974	RD-1003HL		
1975	RD-1001L		
1975	RD-2004		
1975	RD-1001		
1976	RD-1002L		
1976	RD-2004L		
1976	RD-1002		
1976	RD-2004F		
1977	RD-1004L		
1977	RD-1004		
1977	RD-1004LD		
1977	RD-1004HL		
1978	RD-1004V		
1978	RD-1005L		
1978	RD-1005LA		
1978	RD-1200HL		
1978	RD-1200HLD		
1979	RD-560LK		
1979	RD-560LW		
1979	RD-1400L		
1979	RD-800L		
1979	RD-500HL		
1980	RD-800F		
1980	RD-561LK		
1980	RD-900		
1980	RD-900L		
1980	RD-670LC		
1980	RD-671LC		
1980	RD-900F		
1980	RD-7100LKT		
1984	RD-672C		
1984	RD-672LC		
1985	RD-1020L		
1985	RD-673LC		
1985	TD-678W		
1985	RD-675C		
1985	RD-1021L		
1990	RD-1022LD		
1990	RD-1023L		
1996	RD-1024LD		
1996	RD-1024L		