

日立ポンプ機種変遷表

1989年(平成1年)以降

機種	年																												該当ページ	
	89	90	91	92	93	94	95	96	97	98	99	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16		17
80W・単相	WT-P80F	WT-P80H	WT-P80J																										—	
125・150W単相	WT-P125F	WT-P125H	WT-P125J	WT-P125S	WT-P125V	WT-P125W	WT-P125X																						P13	
	WT-P125	WM-P125H	WM-P125J	WM-P125S	WM-P125V	WM-P125W	WM-P150X*																						P16	
200・250W単相	WT-P200G	WT-P200H	WT-P200J,PL200J	WT-P200S	WT-P200V	WT-P200W	WT-P200X																						P14	
	WT-P200	WM-P200H	WM-P200J	WM-P200S	WM-P200V	WM-P200W	WM-P250X*																						P16	
	WT-K200F	WT-K200H	WT-K200J	WT-K200S	WT-K200V	WT-K200W	WT-K200X																						P14	
	WT-P300F	WT-P300H	WT-P300J,PL300J	WT-P300S	WT-P300V	WT-P300W	WT-P300X																						P14	
	WT-P400F	WT-P400H	WT-P400J	WT-P400S	WT-P400V	WT-P400W	WT-P400X																						P15	
	WT-P400	WM-P400H	WM-P400J	WM-P400S	WM-P400V	WM-P400W	WM-P400X*																						P17	
400W・三相	WT-K400F	WT-K400H	WT-K400J																						P15					
	WT-K400	WM-K400H	WM-K400J	代替機種 WT-K750W*	WT-K750X*																									P17
750W・三相	WT-K750F	WT-K750H	WT-K750J	WT-K751J	WT-K750S	WT-K750V	WT-K750W	WT-K750X																						P15
	WT-K750	WM-K750H	WM-K750J	WM-K751J	WM-K750S*	WM-K750V*	WM-K750W*	WM-K750X*																						P17
150W・単相	CT-P150F	CT-P150H	CT-P150J	CT-P150S	CT-P150V	CT-P150W																						P21		
	CM-P250F																										CM-P250X*	P26		
250W・単相	CT-P250F	CT-P250H	CT-P250J	CT-P250S	CT-P250V	CT-P250W																						P22		
	CT-K250F	CT-K250H	CT-K250J	CT-K250S	CT-K250V	CT-K250W																						P22		
400W・単相	CT-P400F	CT-P400H	CT-P400J	CT-P400S	CT-P400V	CT-P400W																						P23		
	DM-P400	DM-P400J	DM-P400S*	DM-P400V*	DM-P400W*	CM-P400X*																						P27		
400W・三相	CT-K400F	CT-K400H	CT-K400J																						P25					
	DM-K400	代替機種 CT-K750W*	代替機種 DM-K750W*	CM-K750X*																									P29	
600W・単相	CT-P600F	CT-P600H	CT-P600J	CT-P600S	CT-P600V	CT-P600W																						P24		
	DM-P600	DM-P600J	DM-P600S*	DM-P600V*	DM-P600W*	CM-P600X*																						P28		
750W・三相	CT-K750F	CT-K750H	CT-K750J	CT-K750S	CT-K750V	CT-K750W																						P25		
	DM-K750	DM-K750J	DM-K750S*	DM-K750V*	DM-K750W*	CM-K750X*																						P29		

※印は代替機種なので従来の機種と寸法、仕様が異なる場合があります。買い替えに当たっては寸法、仕様をご確認ください。

機種	年																												該当ページ
	89	90	91	92	93	94	95	96	97	98	99	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	
100W・10L	PUS-10F																											P40	
	CX-220D	CX-110H	CX-110J	CX-110NS	CX-110V	CX-110W																							
	CX-320D																												
200L	UB-200	UB-200H	UB-200J	UB-200S	UB-200V	UB-200W																						P41	
	500L	UB-500	UB-500H	UB-500J	UB-500S	UB-500V	UB-500W																						
400W																											P40		
	40F-P401, K401																												
750W																											P40		
	40F-K751	40F-K752	40F-K750W																										
400W	40FM-P(B)400XR,D	40FM-P(B)401R,D	40FM-P(B)402R,D	40FM-PR(PD)400V	40FM-PR(PD)400W																						P38 (P37)		
	40FM-K(B)400XR,D	40FM-KB401R	40FM-KB751R*	40FM-KR750V*	40FM-KR752R*	40FM-KR750W*																							
400W	40FM-K401R,D	40FM-KB401D	40FM-KB751D	40FM-K751R*	40FM-KR(B)750V*	40FM-KR(KD)750W*																						P38 (P37)	
	40FM-P401S	40FM-P402S	40FM-PS400V	40FM-PS400W																									
400W	40FM-K401S	40FM-K751S*	40FM-K752S*	40FM-KS750V*	40FM-KS750W*																						P39		
	PL-400A	40FM-P401S*	40FM-P402S*	40FM-PS400V*	40FM-PS400W*																								
600W	PL-600A	40FM-P401S*	40FM-P402S*	40FM-PS400V*	40FM-PS400W*																						P39		
	40FM-K(B)750XR,D	40FM-K(B)751R,D	40FM-KR(KD)750V	40FM-KR(KD)750W																						P38 (P37)			
750W・三相	40FM-K(B)750XR,D	40FM-K(B)751R,D	40FM-K(B)752R,D	40FM-KS750V*	40FM-KS750W*																						P39		
	40FM-K751S	40FM-K752S	40FM-KS750V*	40FM-KS750W*																									
40W	PL-K750A	40FM-K751S*	40FM-K752S*	40FM-KS750V*	40FM-KS750W*																						P39		
	H-PB41FD	H-PB41FH	H-PB40FJ	H-PB40FS	H-PB40FV	H-PB40FW																						P42	
100W	H-PBH100FD	H-PBH100FH	H-PB100FJ	H-PB100FS	H-PB100FV	H-PB100FW																						P42	
	15W	H-PB15D	H-PB15H	H-PB15J																									—
40W	H-PB40FT	H-PB40H	H-PB40J	H-PB40S	H-PB40V	H-PB40W																						P48	
	80W	H-PB80FT	H-PB80H	H-PB80J	H-PB80S	H-PB80V	H-PB80W																						P48
150W	H-P150D	H-P150H	H-P150J	H-P150S	H-P150V	H-P150W																						P48	
	250W	H-P250D	H-P250H	H-P250J	H-P250S	H-P250V	H-P250W																						P48
井戸用浄水器	PE-25F	PE-25H	PE-25J	PE-25S	PE-25NS	PE-25V	PE-25W																						P45
	井戸用除菌器	CS-20E	CS-20H	CS-20J	CS-20NS	CS-30S	CS-30V	CS-130W																					
除鉄除菌システム用除鉄槽	FE-10S	FE-10H	FE-10J	FE-10NS	FE-10V	FE-10W																						P47	
	FE-10V1																												