

# 日立ポンプ機種変遷表

1984年(昭和59年)以降

機種	年度	1985	1986	1987	1988	1989	1990	1991	1992	1993	1994	1995	1996	1997	1998	1999	2000	2001	2002	2003	2004	2005	2006	2007	2008	2009	2010	2011	該当ページ
	機種	昭和60	61	62	63	平成1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	
浅井戸用自動ポンプ	80W・単相	WT-P80F			WT-P80H			WT-P80J			代替機種 WT-P125S			代替機種 WT-P125V			P15												
	125W・単相	WT-P125F			WT-P125H			WT-P125J			WT-P125S			WT-P125V			P15												
		WM-P125			WM-P125H			WM-P125J			WM-P125S			WM-P125V			P16												
	200W・単相	WT-P200F	WT-P200G			WT-P200H			WT-P200J			WT-P200S			WT-P200V			P15											
		WM-P200			WM-P200H			WM-P200J			WM-P200S			WM-P200V			P16												
	200W・三相	WT-K200F			WT-K200H			WT-K200J			WT-K200S			WT-K200V			P15												
	300W・単相	WT-P300F			WT-P300H			WT-P300J			WT-P300S			WT-P300V			P15												
	400W・単相	WT-P400F			WT-P400H			WT-P400J	WT-P401J	WT-P400S			WT-P400V			P15													
					WM-P400H			WM-P400J	WM-P401J	※WM-P400S			※WM-P400V			P17													
					WM-P400H			WM-P400J	WM-P401J	※WM-P400S			※WM-P400V			P17													
400W・三相	WT-K400F			WT-K400H			WT-K400J	代替機種 WT-K750S			WT-K750V			P15															
				WM-K400H			WM-K400J	※WM-K750S			※WM-K750V			P17															
				WM-K400H			WM-K400J	※WM-K750S			※WM-KH750V			P17															
750W・三相	WT-K750F			WT-K750H			WT-K750J	WT-K751J	WT-K750S			WT-K750V			P15														
				WM-K750H			WM-K750J	WM-K751J	※WM-K750S			※WM-K750V			P17														
				WM-K750H			WM-K750J	WM-K751J	※WM-K750S			※WM-KH750V			P17														
浅深両用・深井戸用自動ポンプ	150W・単相	CT-P150F			CT-P150H			CT-P150J			CT-P150S			CT-P150V			P19												
	250W・単相	CM-P250F																											
		CT-P250F			CT-P250H			CT-P250J			CT-P250S			CT-P250V			P19												
	250W・三相	CT-K250F			CT-K250H			CT-K250J			CT-K250S			CT-K250V			P19												
	400W・単相	CT-P400F			CT-P400H			CT-P400J			CT-P400S			CT-P400V			P19												
	400W・三相				DM-K400J			※DM-K750S			※DM-K750V			※DM-KH750V			P21												
		CT-K400F			CT-K400H			CT-K400J			代替機種 CT-K750S			CT-K750V			P20												
	600W・単相				DM-P600J			※DM-P600S			※DM-P600V			※DM-PH600V			P21												
		CT-P600F			CT-P600H			CT-P600J			CT-P600S			CT-P600V			P20												
	750W・三相				DM-K750J			※DM-K750S			※DM-K750V			※DM-KH750V			P21												
	CT-K750F			CT-K750H			CT-K750J			CT-K750S			CT-K750V			P20													

※印機種はH型・J型ポンプと押し高さが異なりますので、仕様を確認してください。

機種	年度	1985	1986	1987	1988	1989	1990	1991	1992	1993	1994	1995	1996	1997	1998	1999	2000	2001	2002	2003	2004	2005	2006	2007	2008	2009	2010	2011	該当ページ
	機種	昭和60	61	62	63	平成1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	
水道加圧装置(受水槽つき)	200W・300L	PUS-320F1	PUS-320LG			PUS-320LH			PUS-320LJ			※UB-200SとWT-P200Sの組み合わせ			※UB-200VとWT-P200Vの組み合わせ			P25											
	300W・300L	PUS-330F1			PUS-330LH			PUS-330LJ			※UB-200SとWT-P300Sの組み合わせ			※UB-200VとWT-P300Vの組み合わせ			P25												
	200W・500L	PUS-520F1	PUS-520LG						※UB-500SとWT-P200Sの組み合わせ			※UB-500VとWT-P200Vの組み合わせ			P25														
	300W・500L	PUS-530F1						※UB-500SとWT-P300Sの組み合わせ			※UB-500VとWT-P300Vの組み合わせ			P25															
	100W・10L	PUS-10F																											
	100W・10L	CX-220D			CX-110H			CX-110J			CX-110NS			CX-110V			P26												
		CX-320D																											
加圧装置用受水槽	200L	UB-200			UB-200H			UB-200J			UB-200S			UB-200V			P25												
	500L	UB-500			UB-500H			UB-500J			UB-500S			UB-500V			P25												
	500L	Z-500																											
	1,000L				UBT-500H			UBT-500J			UBT-500V																		
	1,500L				UBT-1000H			UBT-1000J			UBT-1000V																		
	2m³				UBT-1500H			UBT-1500J			UBT-1500V																		
	3m³				HGT-2000																								
	4m³				HGT-3000																								
					HGT-4000																								
給水装置(非自給)	400W				40F-P401			40F-K401																					
	750W				40F-K751			40F-K752			40F-K750V						P24												
	400W	40FM-P(B)400×R,D			40FM-K(B)400×R,D			40FM-P(B)401R,D			40FM-P(B)402R,D			40FM-PR(PD)400V			P23												
								40FM-KB401R			※40FM-KB751R			※40FM-KR750V			P23												
								40FM-K401R,D			40FM-KB401D			※40FM-KB751D,40FM-K751R			※40FM-KR(KD)750V	P23											
								40FM-P401S			40FM-P402S			40FM-PS400V			P24												
								40FM-K401S			※40FM-K751S			※40FM-K752S			※40FM-KS750V	P24											
		PL-400A						※40FM-P401S			※40FM-P402S			※40FM-PS400V			P24												
	600W	PL-600A						※40FM-P401S			※40FM-P402S			※40FM-PS400V			P24												
	750W・三相	40FM-K(B)750×R,D						40FM-K(B)751R,D			40FM-K(B)752R,D			40FM-KR(KD)750V			P23												
							40FM-K751S			40FM-K752S			40FM-KS750V			P24													
	PL-K750A						※40FM-K751S			※40FM-K752S			※40FM-KS750V			P24													
温水循環ポンプ	15W	H-PB15D			H-PB15H			H-PB15J																					
	40W	H-PB40F			H-PB40H			H-PB40J			H-PB40S			H-PB40V			P31												
	80W	H-PB80F			H-PB80H			H-PB80J			H-PB80S			H-PB80V			P31												
	150W	H-P150D			H-P150H			H-P150J			H-P150S			H-P150V			P31												
	250W	H-P250D			H-P250H			H-P250J			H-P250S			H-P250V			P31												

※印は推奨機種ですが、寸法等は異なります。寸法図等で確認してください。