







日立ポンプ機種変遷表

1993年(平成5年)以降

年	93	94	95	96	97	98	99	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	該当 ページ
機種	平成 5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	令和 2	3	4	
浅井戸用自動ポンプ	80W・ 単相	WT-P80H	WT-P80J																										—		
	125・ 150W 単相	WT-P125H	WT-P125J		WT-P125S	WT-P125V	WT-P125W	WT-P125X	WT-P125Y																		P12				
		WM-P125H	WM-P125J		WM-P125S	WM-P125V		WM-P125W	WM-P150X*	WM-P150Y*																		P15			
	200・ 250W 単相																														
		WT-P200H	WT-P200J, PL200J		WT-P200S	WT-P200V	WT-P200W	WT-P200X	WT-P200Y																		P13				
		WM-P200H	WM-P200J		WM-P200S	WM-P200V		WM-P200W	WM-P250X*	WM-P250Y*																		P15			
		200W・ 三相	WT-K200H	WT-K200J		WT-K200S	WT-K200V	WT-K200W	WT-K200X	WT-K200Y																		P13			
			WM-K200H	WM-K200J		WM-K200S		WM-K200V		WM-K200X																		P16			
		300W・ 単相	WT-P300H	WT-P300J, PL300J		WT-P300S	WT-P300V	WT-P300W	WT-P300X	WT-P300Y																		P13			
	WM-P300H		WM-P300J		WM-P300S	WM-P300V		WM-P300W		WM-P300X																		P16			
400W・ 単相	WT-P400H	WT-P400J	WT-P401J	WT-P400S	WT-P400V	WT-P400W	WT-P400X	WT-P400Y																		P14					
	WM-P400H	WM-P400J	WM-P401J	WM-P400S*	WM-P400V*		WM-P400W*	WM-P400X*	WM-P400Y*																		P16				
400W・ 三相	WT-K400H	WT-K400J		代替機種				WT-K750W*	WT-K750X*	WT-K750Y*																		P14			
	WM-K400H	WM-K400J		代替機種				WM-K750W*	WM-K750X*	WM-K750Y*																		P16			
750W・ 三相	WT-K750H	WT-K750J	WT-K751J	WT-K750S	WT-K750V	WT-K750W	WT-K750X	WT-K750Y																		P14					
	WM-K750H	WM-K750J	WM-K751J	WM-K750S*	WM-K750V*		WM-K750W*	WM-K750X*	WM-K750Y*																		P16				
150W・ 単相	CT-P150H	CT-P150J		CT-P150S	CT-P150V	CT-P150W	CT-P150X	CT-P150Y																		P19					
	DM-P150H	DM-P150J		DM-P150S	DM-P150V		DM-P150X																		P24						
250W・ 単相	CT-P250H	CT-P250J		CT-P250S	CT-P250V	CT-P250W	CT-P250X	CT-P250Y																		P20					
	DM-P250H	DM-P250J		DM-P250S	DM-P250V		DM-P250W		DM-P250X																		P24				
250W・ 三相	CT-K250H	CT-K250J		CT-K250S	CT-K250V	CT-K250W	CT-K250X	CT-K250Y																		P20					
	DM-K250H	DM-K250J		DM-K250S	DM-K250V		DM-K250W		DM-K250X																		P24				
400W・ 単相	CT-P400H	CT-P400J		CT-P400S	CT-P400V	CT-P400W	CT-P400X	CT-P400Y																		P21					
	DM-P400H	DM-P400J		DM-P400S*	DM-P400V*		DM-P400W*	CM-P400X*	CM-P400Y*																		P25				
400W・ 三相	CT-K400H	CT-K400J		代替機種				CT-K750W*	CT-K750X	CT-K750Y																		P23			
	DM-K400H	DM-K400J		代替機種				DM-K750W*	CM-K750X*	CM-K750Y*																		P27			
600W・ 単相	CT-P600H	CT-P600J		CT-P600S	CT-P600V	CT-P600W	CT-P600X	CT-P600Y																		P22					
	DM-P600H	DM-P600J		DM-P600S*	DM-P600V*		DM-P600W*	CM-P600X*	CM-P600Y*																		P26				
750W・ 三相	CT-K750H	CT-K750J		CT-K750S	CT-K750V	CT-K750W	CT-K750X	CT-K750Y																		P23					
	DM-K750H	DM-K750J		DM-K750S*	DM-K750V*		DM-K750W*	CM-K750X*	CM-K750Y*																		P27				

年	93	94	95	96	97	98	99	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	該当 ページ
機種	平成 5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	令和 2	3	4	
パワースターン	100W・ 10L	CX-110H	CX-110J		CX-110NS		CX-110V		CX-110W								CX-110X						P36								
		UB-200H	UB-200J		UB-200S		UB-200V		UB-200W								UB-200X						P37								
受水槽	500L	UB-500H	UB-500J		UB-500S		UB-500V		UB-500W								UB-500X						P37								
		400W	40F-P401, K401																										—		
非自動給水装置	750W	40F-K751		40F-K752		40F-K750V		40F-K750W								40F-K750X						P36									
		40FM-P(B)401R, D		40FM-P(B)402R, D		40FM-PR(PD)400V		40FM-PR(PD)400W								40FM-PR(PD)400X						40FM-PW400Y*	P33								
自動給水装置	400W	40FM-KB401R		40FM-KB751R*		40FM-KB752R*		40FM-KR750W*								40FM-KR750X						40FM-KW750Y*	P33								
		40FM-K401R, D		40FM-KB401D		40FM-KB751D, 40FM-K751R*		40FM-K(B)752R, D*		40FM-KR(KD)750W*								40FM-KR(KD)750X						40FM-KW750Y*	P33						
給湯加圧ポンプ	40W	H-PB41FH		H-PB40FJ		H-PB40FS		H-PB40FV		H-PB40FW								H-PB40FX						P38							
		H-PBH100FH		H-PB100FJ		H-PB100FS		H-PB100FV		H-PB100FW								H-PB100FX						P38							
非自動温水循環ポンプ	15W	H-PB15H		H-PB15J																										—	
		H-PB40H		H-PB40J		H-PB40S		H-PB40V		H-PB40W								H-PB40X						P44							
水処理器	80W	H-PB80H		H-PB80J		H-PB80S		H-PB80V		H-PB80W								H-PB80X						P44							
		H-P150H		H-P150J		H-P150S		H-P150V		H-P150W								H-P150X						P44							
井戸用浄水器	250W	H-P250H		H-P250J		H-P250S		H-P250V		H-P250W								H-P250X						P44							
		PE-25H		PE-25J		PE-25NS		PE-25V		PE-25W								PE-25X						P41							
井戸用除菌器	150W	CS-20H		CS-20J		CS-20NS		CS-30V		CS-130W								CS-130X						P42							
		FE-10H		FE-10J		FE-10NS		FE-10V		FE-10W								FE-10X						P43							

※印は代替機種なので従来の機種と寸法、仕様が異なる場合があります。買い替えの際には寸法、仕様をご確認ください。