

石綿(アスベスト)含有部品使用の掃除機 型式一覧表(1)

型式					
C-V125	CV-90	CV-920CK	CV-7710	CV-F110TA	CV-FX270T
C-V140	CV-90A	CV-1901T	CV-7715	CV-F130	CV-FX270Y
C-V140D	CV-90E	CV-1901TB	CV-7716	CV-F130T	CV-FX300
C-V150P	CV-95	CV-2000	CV-7800	CV-F135	CV-FX300T
C-V155	CV-95A	CV-6500	CV-7803	CV-F135T	CV-FX301
C-V156	CV-95E	CV-6550	CV-7805	CV-F150	CV-FX301T
C-V160	CV-95EA	CV-6601	CV-8500	CV-F150T	CV-FX310
C-V160D	CV-95S	CV-6602	CV-8500D	CV-F155	CV-FX310T
C-V165	CV-97	CV-6603	CV-8505	CV-F155T	CV-FX311
C-V168	CV-97A	CV-6603A	CV-8505D	CV-F160T	CV-FX311T
C-V170P	CV-97WD	CV-6603E	CV-8505E	CV-F165T	CV-FX350
C-V170PD	CV-98MC	CV-6605	CV-8510	CV-F165TN	CV-FX3505D
C-V170PDE	CV-98MC2	CV-6607	CV-8510D	CV-F170	CV-FX3505T
C-V190	CV-98W	CV-6608	CV-8510T	CV-F170T	CV-FX350D
C-V280	CV-98WF	CV-6611	CV-8515	CV-F175L	CV-FX350T
C-V300	CV-98WF2	CV-6612	CV-8520	CV-F180T	CV-FX350TS
C-V330	CV-98WH	CV-6612A	CV-8520T	CV-F190	CV-FX355
C-V500	CV-98WH2	CV-6615	CV-8600	CV-F190T	CV-FX355D
C-V500D	CV-101	CV-6650	CV-8605	CV-F195	CV-FX355DS
C-V510	CV-102	CV-6801	CV-8610	CV-F195T	CV-FX355T
C-V510E	CV-102E	CV-6802	CV-8610T	CV-F195TC	CV-FX355Y
C-V550	CV-103E	CV-6802A	CV-8620	CV-F197TC	CV-FX530
C-V550D	CV-107E	CV-7400	CV-8900	CV-F200	CV-FX530D
C-V560	CV-108E	CV-7403	CV-8901	CV-F200T	CV-FX530DS
C-V800	CV-110D	CV-7405	CV-8903	CV-F205	CV-FX530TS
C-V800B	CV-145D	CV-7407	CV-8905	CV-F205T	CV-GT13
C-V850	CV-171P	CV-7411	CV-AX60P	CV-F210T	CV-GT13B
CF-V100D	CV-301D	CV-7415	CV-AX60Y	CV-F215T	CV-MX100
CF-V100S1	CV-301T	CV-7501	CV-AX70P	CV-F220	CV-MX100D
CF-V100S2	CV-511	CV-7502	CV-AX550D	CV-F220T	CV-MX100DB
CF-V100S3	CV-600C	CV-7502A	CV-AX550DS	CV-FX32T	CV-MX100T
CF-V100S4	CV-600CP	CV-7502N	CV-AX550Y	CV-FX33	CV-MX110D
CF-V100W	CV-601	CV-7503	CV-AX550YS	CV-FX33D	CV-MX110Y
CV-6E	CV-605	CV-7503A	CV-AX740D	CV-FX33DS	CV-PF40WD
CV-6J	CV-611	CV-7505	CV-AX750D	CV-FX33T	CV-PS10
CV-7E	CV-680	CV-7506	CV-AX750DS	CV-FX230	CV-PS11
CV-7EA	CV-680B	CV-7508	CV-AX750Y	CV-FX230T	CV-PS11B
CV-8E	CV-680E	CV-7516	CV-AX750YS	CV-FX230TS	CV-PS11ES
CV-8EB	CV-700	CV-7550	CV-AX760D	CV-FX235	CV-PS50WD
CV-9	CV-700B	CV-7550A	CV-AX760DS	CV-FX235T	CV-RX1
CV-9A	CV-700E	CV-7600	CV-AX760Y	CV-FX235TC	CV-S1
CV-9E	CV-701	CV-7605	CV-EX5300	CV-FX235TS	CV-TN10
CV-9G	CV-800E	CV-7606	CV-F1	CV-FX240D	CV-TN10E
CV-9H	CV-801	CV-7616	CV-F10	CV-FX250	CV-TN95
CV-9P	CV-880	CV-7623	CV-F23	CV-FX250T	D-100T
CV-11	CV-880D	CV-7700	CV-F100	CV-FX251	D-101T
CV-15	CV-885	CV-7700B	CV-F100D	CV-FX251T	D-102T
CV-20	CV-886	CV-7701	CV-F100T	CV-FX260D	D-103T
CV-20D	CV-900C	CV-7702	CV-F100TA	CV-FX260T	D-105T
CV-20EL	CV-900CA	CV-7702A	CV-F105	CV-FX261T	D-106T
CV-30D	CV-910C	CV-7703	CV-F108T	CV-FX270	D-50M
CV-40D	CV-910CA	CV-7705	CV-F110	CV-FX270D	D-70M
CV-45P	CV-910CP	CV-7706	CV-F110T	CV-FX270DS	D-80M

石綿(アスベスト)含有部品使用の掃除機 型式一覧表(2)

型式
D-85M
D-90M
D-TK1
H-H10
H-H12
PV-A1
PV-A2
PV-A10
PV-AD10
PV-B1
PV-B2
PV-B3
PV-B10
R-H3000
R-H3000D
R-H3100
R-H3200
R-H3210
R-H5300
R-H5500
R-H5600
R-H6000
R-H6000D
R-H6100
R-H7500
R-H7500E
R-H8000
R-H8000D
R-H8100
R-H8200
R-H8800
R-V7000
R-V7000A
R-V7200
SB-R201
SC-R352
SF-R202
SF-R304
SF-R352