






グラファイトヒーター1200W+PTCヒーター1200W=2400W)  
(24時間換気対応型) 強弱仕様

[illegible]

メインリモコン:HBK-1210-RE



Technical drawing of the TAC3000 control panel. The front view shows a rectangular panel with a width of 45 and a height of 90. The panel features five buttons: a red button for '入浴暖房' (Bath Heating) with '暖房' (Heating) below it, a blue button for '浴温' (Bath Temperature) with '設定' (Setting) below it, a yellow button for '換気' (Ventilation) with '強風' (Strong Wind) below it, a white button for '人感オート' (Person Sensor Auto) with 'タイマー' (Timer) below it, and a red button for '停止' (Stop) with '24時間以上(3分間)' (24 hours or more (3 minutes)) below it. At the bottom of the panel, it says '3行TAC3000' and 'H204034-1V'. The side view shows a depth of 14.

- ・グラファイトヒーター (600W×2本=1200W)
- ・PTCセラミックヒーター (1200W×1本=1200W)
- ・2モーター、2ファン方式
- ・電源コード1.2m
- ・ダクト接続口、3カ所より1カ所選択
- ・高密封風逆流防止弁付
- ・防水形メインリモコン(付属)
- ・防水形サブリモコン(付属)
- ・電源部温度ヒューズ付
- ・過熱防止用温度ヒューズ付
- ・過熱防止用サーミスタ付
- ・適合ダクト径:φ100
- ・取付可能開口寸法:角穴100×100~250×480(mm)
- ・新規開口寸法:丸穴φ100~φ250(mm)

品番	品 名	材 質	備 考
1	パネル	P P	ホワイ
2	取付ベース板	SUS	
3	排気ダクト口	SUS/ABS	3カ所より1カ所選択
4	逆止弁	P P	
5	ヒーターカバー	SUS	
6	電源コード取出口		3カ所より1カ所選択
7	電源コード		コード長1.2m
8	フィルター	P P	
9			
10			
11			
12			

機種名	浴室乾燥暖房機
型 式	HBK-2250SK

\*製品の仕様は、改良のため予告なしに変更することがありますのでご了承ください。